



Safety cabinets, Class II,
Thermo Scientific Heraeus® HERAsafe® KS

Thermo
SCIENTIFIC

51

2 yr

Catalogue No	Alt. No	Model No
BPG-950-010K	51021153	KS9
BPG-950-020H	51021154	KS12
BPG-950-030E	51021155	KS15
BPG-950-040B	51021156	KS18

Accessories

Catalogue No	Alt. No	Description
BPG-950-500Q	50073771	KDD-12/15 connection to fixed ducting with visible anti-blowback flap
BPG-950-504Y	50072119	KFS 19 floor stand 680mm high (working height 750mm)
BPG-950-508A	50073656	KFS 112 floor stand 680mm high
BPG-950-510N	50072142	KFS 115 floor stand 680mm high
BPG-950-512J	50073657	KFS 118 floor stand 680mm high
BPG-950-514F	50073585	KFS 209 floor stand. Adjustable in 50mm steps, 750 to 950mm
BPG-950-516B	50073582	KFS 212 floor stand. Adjustable in 50mm steps, 750 to 950mm
BPG-950-518U	50073583	KFS 215 floor stand. Adjustable in 50mm steps, 750 to 950mm
BPG-950-520K	50073584	KFS 218 floor stand. Adjustable in 50mm steps, 750 to 950mm
BPG-950-558Y	50078791	KDD-9 connection to fixed ducting with visible anti-blowback flap
BPG-950-560V	50078790	KDD 18 connection to fixed ducting with visible anti-blowback flap
BPG-950-562R	50073962	SPOT K, UV-C irradiator for rear wall mounting. Requires UV socket
BPG-100-540L	50048696	UV-C 30, for sterilising the work chamber in all HERAsafe® models, with protective cover

Factory fitted options - please see side panel for ordering information.

These are only some of the options available for your cabinet. Please contact Customer Service (contact details are given on the inside front cover) who will be happy to offer further advice as to what is available, discuss your decontamination requirements and be able to advise of the cost of installation and commissioning, which is extra to the above prices.

Catalogue No	Description
50044679	Water tap for installation in side wall
50045959	Non-flammable gas tap for installation in side wall
50046015	Flammable gas tap for installation in side wall
50074905	Solenoid operated valve must be used when flammable gases are used
51900303	UK electrical socket type (3-pin) for all cabinets (German standard supplied if not ordered)
51900642	UV-C irradiator in side walls (4 x 15W tubes, 2 on each side)
51900643	Special socket in right hand side wall for fitting of UV systems above. Replaces one of the standard electrical sockets outlets.
51900648	Rear wall coated grey-white over stainless steel (anti-reflection)
51900657	AEF additional exhaust filter for recirculation with HG 3 material

Decontamination options

Catalogue No	Alt. No	Description	For models
BPG-950-528R	VAP-1a	Formalin vapouriser only (no neutralisation), 120mL capacity	All
BPG-950-534W	KS-VAP-3	Formonia decontamination/neutralisation unit with 6 disposable charcoal filters. Also requires KSNB top box on recirculating cabinets	All
BPG-950-540E	KSF-9	Mounting frame to allow fitting of all top box options	KS9
BPG-950-542A	KSF-12/15	Mounting frame to allow fitting of all top box options	KS12/15
BPG-950-544T	KSP(FD)-9	Top box plate with 3m of 160mm diameter flexible trunking for removal of fumigant	KS9
BPG-950-546P	KS 12/15	Top box plate with 3m of 160mm diameter flexible trunking for removal of fumigant	KSP(FD)-12/15
BPG-950-548L	KSP(FD)-18	Top box plate with 3m of 160mm diameter flexible trunking for removal of fumigant	KS18
BPG-950-550B	KSNB-9	Neutralisation top box for Formonia unit	KS9
BPG-950-552U	KSNB-12/15	Neutralisation top box for Formonia unit	FS12/15
BPG-950-554Q	KSNB-18	Neutralisation top box for Formonia unit	KS18
BPG-950-556M	VAP-3-VN	Formonia unit only without charcoal filters (for ducted units)	All

**Factory Fitted Options
Ordering Procedure**

- 1) Specify catalogue number of option(s) required to be factory fitted
- 2) Place your order in the usual manner

The prices given include fitting. Should you have any queries please contact Customer Service.

ATTENTION
FACTORY FITTED OPTIONS MUST BE SPECIFIED AT THE TIME OF ORDERING THE MAIN UNIT